


**Screw-on toolholder set, left-hand, Shank / insert size: 16mm**

**Order data**

Order number	255131 16
GTIN	4045197941749
Item class	29W

**Technical description**

Head length L <sub>1</sub>	22 mm
Head length L <sub>1</sub>	25 mm
Head length L <sub>1</sub>	25 mm
Overall length L	100 mm
suitable indexable insert	CN.. 09T3.; DN.. 1104.; SN.. 1204..
ISO code toolholder	PCLNL 1616H09; PDJNL 16161H11; PSSNL 1616H12
Shank size	16 mm
Functional width L <sub>4</sub>	20 mm
Series	QuickTurn
Spare part	259981 1
Standard	DIN ISO 5610

Standard	Works standard
Application type	left-hand
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Spare parts set for lever lock toolholder Type 1	259981 1
Lever lock toolholder Shank / insert size 16/11 mm	250611 16/11
Lever lock toolholder Shank / insert size 16/12 mm	251113 16/12
Lever lock toolholder Shank / insert size 16/09 mm	250019 16/09