



Screw-on toolholder set, right-hand, Shank / insert size: 20mm



Order data

Order number	255130 20
GTIN	4045197941725
Item class	29W

Technical description

suitable indexable insert	CN.. 1204.; DN.. 1104.; SN.. 1204..
Functional width L ₄	25 mm
Overall length L	125 mm
Series	QuickTurn
Shank size	20 mm
ISO code toolholder	PCLNR 2020K12; PDJNR 2020K11; PSSNR 2020K12
Head length L ₁	25 mm
Spare part	259981 2
Standard	DIN ISO 5610
Standard	Works standard
Application type	right-hand

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Spare parts set for lever lock toolholder Type 2	259981 2
Lever lock toolholder Shank / insert size 20/11 mm	250610 20/11
Lever lock toolholder Shank / insert size 20/12 mm	250018 20/12
Lever lock toolholder Shank / insert size 20/12 mm	251112 20/12