



Screw-on toolholder set, left-hand, Shank / insert size: 20mm



Order data

Order number	255131 20
GTIN	4045197941756
Item class	29W

Technical description

Series	QuickTurn
Overall length L	125 mm
suitable indexable insert	CN.. 1204..; DN.. 1104..; SN.. 1204..
Head length L ₁	25 mm
Functional width L ₄	25 mm
ISO code toolholder	PCLNL 2020K12; PDJNL 2020K11; PSSNL 2020K12
Shank size	20 mm
Spare part	259981 2
Standard	DIN ISO 5610
Standard	Works standard
Application type	left-hand

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Spare parts set for lever lock toolholder Type 2	259981 2
Lever lock toolholder Shank / insert size 20/12 mm	251113 20/12
Lever lock toolholder Shank / insert size 20/12 mm	250019 20/12
Lever lock toolholder Shank / insert size 20/11 mm	250611 20/11