



## Screw-on toolholder set, left-hand, Shank / insert size: 25mm



### Order data

Order number	265131 25
GTIN	4045197941848
Item class	29W

### Technical description

Overall length L	150 mm
Head length L <sub>1</sub>	20 mm
Head length L <sub>1</sub>	21.5 mm
Head length L <sub>1</sub>	25 mm
suitable indexable insert	CC.. 1204.; DC.. 11T3.; SC.. 1204
ISO code toolholder	SCLCL 2525M12; SDJCL 2525M11; SSSCL 2525M12
Shank size	25 mm
Functional width L <sub>4</sub>	32 mm
Spare part	269981 3
Standard	DIN ISO 5610
Application type	left-hand

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

### Accessories

Spare parts set for screw-on toolholder Type 3	269981 3
Screw-on toolholder Shank / insert size 25/12 mm	260007 25/12
Screw-on toolholder Shank / insert size 25/11 mm	260309 25/11
Screw-on toolholder Shank / insert size 25/12 mm	260707 25/12