



## Screw-on toolholder set, left-hand, Shank / insert size: 25mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 255131 25     |
| GTIN         | 4045197941763 |
| Item class   | 29W           |

### Technical description

|                                 |   |
|---------------------------------|---|
| Overall length L                | 150 mm                                      |
| suitable indexable insert       | CN.. 1606.; DN.. 1506.; SN.. 1204..         |
| Functional width L <sub>4</sub> | 32 mm                                       |
| Shank size                      | 25 mm                                       |
| ISO code toolholder             | PCLNL 2525M16; PDJNL 2525M15; PSSNL 2525M12 |
| Series                          | QuickTurn                                   |
| Head length L <sub>1</sub>      | 25 mm                                       |
| Spare part                      | 259981 3                                    |
| Standard                        | DIN ISO 5610                                |
| Application type                | left-hand                                   |
| Application                     | External longitudinal turning               |
| Application                     | External longitudinal turning               |

Type of product

Boring bar

---

**Accessories**

|  |              |
|--|--------------|
| Spare parts set for lever lock toolholder Type 3   | 259981 3     |
| Lever lock toolholder Shank / insert size 25/15 mm | 250611 25/15 |
| Lever lock toolholder Shank / insert size 25/16 mm | 250019 25/16 |
| Lever lock toolholder Shank / insert size 25/12 mm | 251113 25/12 |