



Screw-on toolholder set, right-hand, Shank / insert size: 12mm



Order data

Order number	265130 12
GTIN	4045197941770
Item class	29W

Technical description

suitable indexable insert	CC.. 09T3..; DC.. 0702..; SC.. 09T3
ISO code toolholder	SCLCR 1212F09; SDJCR 1212F07; SSSCR 1212F09
Series	QuickTurn
Head length L ₁	13 mm
Head length L ₁	17 mm
Head length L ₁	20 mm
Overall length L	80 mm
Functional width L ₄	16 mm
Shank size	12 mm
Spare part	269981 1
Standard	DIN ISO 5610

Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Spare parts set for screw-on toolholder Type 1	269981 1
Screw-on toolholder Shank / insert size 12/09 mm	260706 12/09
Screw-on toolholder Shank / insert size 12/07 mm	260308 12/07
Screw-on toolholder Shank / insert size 12/09 mm	260006 12/09