



## Screw-on toolholder set, right-hand, Shank / insert size: 25mm



### Order data

Order number	265110 25
GTIN	4045197941930
Item class	29W

### Technical description

Overall length L	150 mm
ISO code toolholder	SCLCR 2525M12; SCSCR 2525M12
suitable indexable insert	CC.. 1204..
Functional width L <sub>4</sub>	32 mm
Shank size	25 mm
Head length L <sub>1</sub>	20 mm
Series	QuickTurn
Spare part	269981 5
Standard	DIN ISO 5610
Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

Spare parts set for screw-on toolholder Type 5

269981 5

Screw-on toolholder Shank / insert size 25/12 mm

260006 25/12

Screw-on toolholder Shank / insert size 25/12 mm

260000 25/12