



## Screw-on toolholder set, right-hand, Shank size: 20mm



### Order data

Order number	255110 20
GTIN	4045197941862
Item class	29W

### Technical description

ISO code toolholder	PCLNR 2020K12; PCSNR 2020K12
Series	QuickTurn
Head length L <sub>1</sub>	28 mm
Functional width L <sub>4</sub>	25 mm
suitable indexable insert	CN.. 1204..
Shank size	20 mm
Overall length L	125 mm
Spare part	259981 5
Standard	Works standard
Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

Spare parts set for lever lock toolholder Type 5

259981 5

Lever lock toolholder Shank / insert size 20/12 mm

250018 20/12