



## Screw-on toolholder set, right-hand, Shank size: 25mm



### Order data

Order number	255110 25
GTIN	4045197941879
Item class	29W

### Technical description

ISO code toolholder	PCLNR 2525M16; PCSNR 2525M16
Overall length L	150 mm
Head length L <sub>1</sub>	33 mm
Shank size	25 mm
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	CN.. 1606..
Series	QuickTurn
Spare part	259981 6
Standard	Works standard
Application type	right-hand
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

Spare parts set for lever lock toolholder Type 6

259981 6

Lever lock toolholder Shank / insert size 25/16 mm

250018 25/16