

**Garant****Grooving insert, HB7010, Groove width w: 0,5mm****Order data**

Order number	273665 0,5
GTIN	4045197942203
Item class	21L

**Description****Application:**

With grooving toolholder for insert width 3 mm.

**Note:**

The tool holders must be suitably reworked to suit the groove width.

**Technical description**

Tool material	Carbide
for retaining ring to DIN471/472	0.4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Groove width w	0.5 mm
$a_r$	1.3 mm
Main application	P
Secondary application	K
Cutting conditions	continuous
Grade	HB7010
Slots to standard	DIN 471

Slots to standard	DIN 472
Number of changes/inserts	2
Indexable insert profile	neutral
Type of product	Indexable insert for grooving

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	230 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable only under restricted conditions	190 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	130 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	150 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	140 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable	70 m/min	S
GG(G)	suitable	200 m/min	K
CuZn	suitable	250 m/min	N
Uni	suitable		
continuous	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		