



## ECO knurling tool right-hand, Shank size: 16 mm



### Order data

Order number	290238 16
GTIN	4030741290459
Item class	29I

### Description

#### Version:

Grub screws in the shank for clearance angle correction.

for knurl profile: RGE30° 2×AA

for knurl  $\varnothing d_1$ : 15 mm

for knurl width w: 4 mm

for knurl bore  $\varnothing d_2$ : 8 mm

Working range: 3 - 50 mm

Carbide sleeve, cover disc, screw: 299920 4

### Technical description

Shank width	16 mm
Working range	3 - 50 mm
for knurl width w	4 mm
Shank height	16 mm
Carbide sleeve, cover disc, screw	299920 4

for knurl bore $\varnothing d_2$	8 mm
for knurl $\varnothing d_1$	15 mm
for knurl profile	RGE45° BL/BR15°
for knurl profile	RGE30° 2×AA
Type of product	Self-centering knurling tool