



ECO knurling tool right-hand, Shank size: 16mm



Order data

Order number	290230 16
GTIN	4030741355615
Item class	29H

Description

Version:

Grub screws in the shank for clearance angle correction.

for knurl profile: RAA 1×BR30°

for knurl $\varnothing d_1$: 15 mm

for knurl width w: 4 mm

for knurl bore $\varnothing d_2$: 8 mm

Working range: 3 - 50 mm

Carbide sleeve, cover disc, screw: 299920 3

Technical description

Carbide sleeve, cover disc, screw	299920 3
Working range	3 - 50 mm
for knurl width w	4 mm
for knurl bore $\varnothing d_2$	8 mm
for knurl $\varnothing d_1$	15 mm

Shank height	16 mm
Shank width	16 mm
for knurl profile	RAA 1×BR30°
Type of product	Self-centering knurling tool