

## Garant

**Face mill arbor cylindrical, with cooling channel bore, SK 40 A = 300, Spigot Ø d1: 16mm**



### Order data

Order number	301139 16
GTIN	4045197942241
Item class	31A

### Description

#### Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With RFID / Balluffchip bore.
- Larger collar contact face.

**Vibration damped version, arbor with vibration-damping core.**

#### Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

#### Supplied with:

Cutter lock screw and drive dog.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

#### Note:

Further sizes on request.

### Technical description

Milling mandrel length $L_4$	17 mm
Spigot Ø d <sub>1</sub>	16 mm
Overhang dimension A	300 mm
Ø D <sub>2</sub>	38 mm
Adapter	SK 40 A = 300
Standard	DIN 6357

Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor