

Garant

Face mill arbor cylindrical, with cooling channel bore, SK 40 A = 200, Spigot Ø d1: 22mm



Order data

Order number	301138 22
GTIN	4045197942227
Item class	31A

Description

Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With RFID / Balluffchip bore.
- Larger collar contact face.

Vibration damped version, arbor with vibration-damping core.

Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

Supplied with:

Cutter lock screw and drive dog.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Note:

Further sizes on request.

Technical description

Spigot Ø d ₁	22 mm
Milling mandrel length L ₄	19 mm
Ø D ₂	48 mm
Overhang dimension A	200 mm
Clamping Ø D ₁	22 mm
Adapter	SK 40 A = 200

Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 8,000 rpm
Concentricity	≤ 6 μm
Machining strategy	HPC
Vibration	damped
Type of product	Milling head arbor