



## Laser distance meter DISTO™, Type: X4



### Order data

Order number	465550 X4
GTIN	7640110697870
Item class	47C

### Description

#### Version:

Impact resistant plastic casing with easy-to-use keypad with symbols. High quality **Leica glass lens** in an particularly temperature-resistant and sturdy **magnesium casing**. Illuminated and rotating colour display for optimum legibility. Power Range Technologie™ for measurements **up to 150 m without target board**. Laser class 2 tested in accordance with ISO 16331-1. The **integral 360° inclination sensor** shows the inclination of an object when the casing is placed directly on it, thus permitting indirect height measurement. Multi-function endpiece for measuring from corners. Dustproof, protected against sprayed water by a rubber seal. Sealed, wash-down keyboard. A robust rubber membrane protects the lens and also provides protection if dropped from a small height.

With **digital target searcher** (4× zoom) for measurements at long distances or in sunshine.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Protective holder and wrist strap. Supplied with 2 batteries No. 081561 size LR6.

#### Note:

Data transfer via Bluetooth® Smart; also by smartphone using a Leica "DISTO™ Plan" app (Android from version 4.3, Apple from iPhone 4s). Easy generation of sketches.

## Technical description

Range	150 m
IP Index of Protection	IP 65
Measuring accuracy	±1.0 mm
Article no of the battery / rechargeable battery fitted	081561 LR6
Addition/subtraction	yes
Interface	Bluetooth interface
Number of batteries contained	2
Recall last measurements	yes
Threaded socket for stand	1/4 UNC in
Clinometer	360 degrees
Surface and volume calculations	yes
Power supply	081561 LR6
multi-function endpiece	yes
Length	132 mm
Weight	184 g
Height	29 mm
Digital target searcher with zoom	4 times
Width	56 mm
indirect measurements (Pythagoras)	yes
Minimum / maximum measurements	yes
Power supply	Battery-powered
Reversible reading	mm / inch
Laser class to IEC 825–1	2
Type of product	Distance meter

## Accessories

Alkaline-manganese batteries International size LR6

081561 LR6