


Garant
Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1: M10X125

Order data

Order number	301309 M10X125
GTIN	4045197943934
Item class	31A

Description
Version:

Plain design.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

L ₂	5 mm
Ø D ₂	18 mm
Overhang dimension A	144 mm
Bore Ø D ₁ tolerance IT6	10.5 mm
External Ø D	34 mm
Thread M	M10×125
Reach L ₁	125 mm
Adapter	SK 40
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor