



## Side lock arbor, HSK-A 100 short, Clamping range $\varnothing$ D1: 40mm



### Order data

Order number	304397 40
GTIN	4045197944269
Item class	32A

### Description

#### Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

#### Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

#### Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

#### Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

### Technical description

External $\varnothing$ D	80 mm
Clamping $\varnothing$ D <sub>1</sub>	40 mm
Spare clamping screw No. 30 9900	32
Overhang dimension A	120 mm
Adapter	HSK-A 100 short
Arbor standard	DIN 69893
Arbor standard	DIN 69882-4
Arbor standard	ISO 12164-1

Shape	A
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing$ D1 32 mm	309900 32
--	-----------