

**Garant**
**Side lock arbor Form ADB with cooling channel bores, SK 30 short, Clamping  
 Ø D1: 12mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 300048 12     |
| GTIN         | 4045197944153 |
| Item class   | 31A           |

**Description**
**Version:**
**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm.  
 With Balluff/RFID chip bore.

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

|                                  |             |
|----------------------------------|-------------|
| Overhang dimension A             | 50 mm       |
| External Ø D                     | 42 mm       |
| Clamping Ø D <sub>1</sub>        | 12 mm       |
| Spare clamping screw No. 30 9900 | 12          |
| Adapter                          | SK 30 short |
| Standard                         | DIN 6359    |
| Arbor standard                   | ISO 7388-1  |

|                                       |                      |
|---------------------------------------|----------------------|
| Shape                                 | ADB                  |
| Cooling channel bore                  | lockable             |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm  |
| Concentricity                         | $\leq 3 \mu\text{m}$ |
| Machining strategy                    | HPC                  |
| Type of product                       | Side lock arbor      |

---

## Accessories

|  |           |
|--|-----------|
| Spare clamping screw for chucks with clamping $\varnothing$ D1 12 mm | 309900 12 |
|--|-----------|