

**Garant**
**Side lock arbor Form ADB with cooling channel bores, SK 30 short, Clamping  
Ø D1: 10mm**

**Order data**

Order number	300048 10
GTIN	4045197944146
Item class	31A

**Description**
**Version:**
**GARANT –**

All shanks hard turned (for smooth cutting action!). Balancing quality G 2.5 / G 25,000 rpm.  
With Balluff/RFID chip bore.

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

**Technical description**

Clamping Ø D <sub>1</sub>	10 mm
Overhang dimension A	50 mm
External Ø D	35 mm
Spare clamping screw No. 30 9900	10
Adapter	SK 30 short
Standard	DIN 6359
Arbor standard	ISO 7388-1

Shape	ADB
Cooling channel bore	lockable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing$ D1 10 mm	309900 10
--	-----------