

Garant**Side lock arbor with cooling channel bore, HSK-A 63 A = 160, Clamping \varnothing D1: 8mm****Order data**

| | |
|--------------|---------------|
| Order number | 304336 8 |
| GTIN | 4045197943323 |
| Item class | 31A |

Description**Version:**

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth running!).

With coolant supply holes that can be plugged.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

| | |
|---------------------------------------|------------------|
| External \varnothing D | 28 mm |
| Spare clamping screw No. 30 9900 | 8 |
| Overhang dimension A | 160 mm |
| Clamping \varnothing D ₁ | 8 mm |
| Adapter | HSK-A 63 A = 160 |

| | |
|---------------------------------------|----------------------|
| Arbor standard | ISO 12164-1 |
| Arbor standard | DIN 69882-4 |
| Arbor standard | DIN 69893 |
| Shape | A |
| Cooling channel bore | lockable |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | $\leq 3 \mu\text{m}$ |
| Machining strategy | HSC |
| Machining strategy | HPC |
| Type of product | Side lock arbor |

Accessories

| | |
|---|----------|
| Spare clamping screw for chucks with clamping \varnothing D1 8 mm | 309900 8 |
|---|----------|