

**HOLEX****Side lock arbor with cooling channel bore, HSK-A 100 short, Clamping  $\varnothing$  D1: 14mm****Order data**

Order number	304398 14
GTIN	4045197944429
Item class	32A

**Description****Version:****With coolant supply holes that cannot be plugged.**

- With RFID/Balluffchip bore.
- HSK mating faces machined.

**Application:**

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

**Optional extras:**

Coolant pipe No. 309880, coolant pipe wrench No. 309890

**Note:**

HSK 40 and 50, Form A and E available ex works by the manufacturer.

**Technical description**

Spare clamping screw No. 30 9900	12
External $\varnothing$ D	44 mm
Clamping $\varnothing$ D <sub>1</sub>	14 mm
Overhang dimension A	80 mm
Adapter	HSK-A 100 short

Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-4
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing$ D1 12 mm	309900 12
--	-----------