

HOLEX**Side lock arbor with cooling channel bore, HSK-A 100 short, Clamping \varnothing D1: 16mm****Order data**

Order number	304398 16
GTIN	4045197944436
Item class	32A

Description**Version:****With coolant supply holes that cannot be plugged.**

- With RFID/Balluffchip bore.
- HSK mating faces machined.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

External \varnothing D	48 mm
Clamping \varnothing D ₁	16 mm
Spare clamping screw No. 30 9900	16
Overhang dimension A	100 mm
Adapter	HSK-A 100 short

Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-4
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 20,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 16 mm	309900 16
--	-----------