

**Garant**
**ER collet chuck mini / slim Form ADB, SK 40 A = 70, for ER collet size: 11**

**Order data**

Order number	300649 11
GTIN	4045197944481
Item class	31A

**Description**
**Version:**

Clamping nut finely balanced **for HSC**. ER11 through bored. Shanks hard turned (smooth cutting action).

· **With Balluffchip bore as standard.**

**Application:**

For clamping tools with plain shank to DIN 6499.

**Supplied with:**

High speed ER mini nut No. 309650.

**Optional extras:**

ER collets No. 308881 – 309434, ER lock wrench No. 309740.

Pull studs (PS) No. 308600 – 308806. PS chuck key No. 308820; 308830.

**Technical description**

Clamping range	0.5 - 7 mm
External Ø D	16 mm
Overhang dimension A	70 mm
for ER collets	11 mm
Suitable chuck key No. 309740	11
Usable length L <sub>N</sub>	44 mm
Clamping Ø D <sub>1</sub>	1-7 mm

Adapter	SK 40 A = 70
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Type of product	Collet chuck

## Accessories

ER colletwith seal Nominal clamping Ø d 4 mm	308882 4
ER collet Nominal clamping Ø d 5 mm	308918 5
ER collet Nominal clamping Ø d 2,5 mm	308881 2,5
ER collet for machine taps Nominal clamping Ø d 4 mm	309399 4
ER collet Nominal clamping Ø d 3 mm	308881 3
ER collet Nominal clamping Ø d 1 mm	308881 1
ER collet for machine taps Nominal clamping Ø d 3,5 mm	309399 3,5
ER collet Nominal clamping Ø d 2 mm	308918 2
ER collet Nominal clamping Ø d 3 mm	308918 3
ER collet Nominal clamping Ø d 4 mm	308881 4
ER collet set 7 pieces 1–7 mm	309155
ER colletwith seal Nominal clamping Ø d 6 mm	308882 6
ER collet Nominal clamping Ø d 1,5 mm	308881 1,5
ER collet Nominal clamping Ø d 5,5 mm	308881 5,5
ER collet for machine taps Nominal clamping Ø d 6 mm	309399 6
ER collet for machine taps Nominal clamping Ø d 4,5 mm	309399 4,5
ER collet Nominal clamping Ø d 6 mm	308881 6
ER collet Nominal clamping Ø d 2 mm	308881 2
ER collet for machine taps Nominal clamping Ø d 2,8 mm	309399 2,8

ER colletwith seal Nominal clamping Ø d 5 mm	308882 5
ER collet Nominal clamping Ø d 6,5 mm	308881 6,5
ER collet Nominal clamping Ø d 4 mm	308918 4
ER collet Nominal clamping Ø d 5 mm	308881 5
ER collet for machine taps Nominal clamping Ø d 2,5 mm	309399 2,5
ER colletwith seal Nominal clamping Ø d 3 mm	308882 3
ER collet Nominal clamping Ø d 1 mm	308918 1
ER collet Nominal clamping Ø d 3,5 mm	308881 3,5
ER collet Nominal clamping Ø d 6 mm	308918 6
ER collet Nominal clamping Ø d 4,5 mm	308881 4,5
ER collet Nominal clamping Ø d 7 mm	308918 7
ER collet set 13 pieces 1–7 mm	309010