

Garant
ER collet chuck mini / slim Form ADB, SK 40 A = 70, for ER collet size: 16

Order data

Order number	300649 16
GTIN	4045197944498
Item class	31A

Description
Version:

Clamping nut finely balanced **for HSC**. ER11 through bored. Shanks hard turned (smooth cutting action).

· **With Balluffchip bore as standard.**

Application:

For clamping tools with plain shank to DIN 6499.

Supplied with:

High speed ER mini nut No. 309650.

Optional extras:

ER collets No. 308881 – 309434, ER lock wrench No. 309740.

Pull studs (PS) No. 308600 – 308806. PS chuck key No. 308820; 308830.

Machining strategy: HSC

Clamping range: 0.5 - 10 mm

External Ø D: 22 mm

Suitable chuck key No. 309740: 16

Technical description

Suitable chuck key No. 309740	16
Clamping range	0.5 - 10 mm
for ER collets	16 mm
External Ø D	22 mm
Usable length L _N	45 mm

Adapter	SK 40 A = 70
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Collet chuck