

**Garant**
**Side lock arbor Form ADB with cooling channel bore, BT 40 short, Clamping  $\varnothing$  D1: 12mm**

**Order data**

Order number	302596 12
GTIN	4045197944627
Item class	31A

**Description**
**Version:**

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

**Technical description**

Spare clamping screw No. 30 9900	12
Clamping $\varnothing$ D <sub>1</sub>	12 mm
External $\varnothing$ D	42 mm
Overhang dimension A	63 mm
Adapter	BT 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	ADB

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping $\varnothing$ D1 12 mm	309900 12
--	-----------