

Garant
Side lock arbor Form ADB with cooling channel bore, BT 50 short, Clamping \varnothing D1: 10mm

Order data

Order number	302650 10
GTIN	4045197944696
Item class	31A

Description
Version:

All shanks hard turned (for smooth running). Balancing quality G2.5 / 25,000 rpm. **With coolant supply holes that can be plugged.**

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	10
External \varnothing D	35 mm
Overhang dimension A	70 mm
Clamping \varnothing D ₁	10 mm
Adapter	BT 50 short
Standard	DIN 6359
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339

Shape	ADB
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 10 mm	309900 10
--	-----------