

Garant**ER collet chuck Form ADB, BT 40 short, for ER collet size: 16****Order data**

Order number	302755 16
GTIN	4045197944788
Item class	31A

Description**Version:**

External and internal taper ground.

- **All shanks hard turned (for smooth running!). Balancing quality G2.5/25,000 rpm.**
- **Clamping nut balanced for HSM (G2.5/25,000 rpm).**
- **Optimum wear characteristics and torque transmission due to the coated precision clamping nut.**

Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

Supplied with:

ER clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309745 or No. 613300.

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Note:

Matching clamping nut No. 309580 or 309610.

Machining strategy: HSC

Clamping range: 0.5 - 10 mm

Overhang dimension A: 70 mm

External Ø D: 28 mm

Spare ER clamping nut: 16

ER chuck key: 16

Technical description

ER chuck key	16
External Ø D	28 mm
for ER collets	16
Overhang dimension A	70 mm
Clamping range	0.5 - 10 mm
Spare ER clamping nut	16
Adapter	BT 40 short
Arbor standard	JIS B6339
Arbor standard	ISO 7388-2
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HSC
Type of product	Collet chuck

Accessories

Single open ended spanner Width across flats 25 mm	613300 25
--	-----------