

Garant
Boring bar, steel, right-hand, Shank \varnothing / insert size: 25/12mm

Order data

Order number	260724 25/12
GTIN	4045197945129
Item class	21T

Technical description

suitable indexable insert	SC.. 1204..
Minimum pre-drill $\varnothing D_{\min}$	32 mm
Insert size	12 mm
Clamping height L_2	24 mm
Overhang L_1	75 mm
ISO code toolholder	A25R SSKCR/L12
Centre offset L_3	17 mm
Pack of insert screws	269028 25
Overall length L	200 mm
Setting angle κ	75 degrees
Shank $\varnothing D_s$	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX20

674248 TX20

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500