

**Garant**
**Boring bar, steel, left-hand, Shank  $\varnothing$  / insert size: 20/09mm**

**Order data**

Order number	260725 20/09
GTIN	4045197945136
Item class	21T

**Technical description**

Clamping height $L_2$	19 mm
Centre offset $L_3$	13 mm
Insert size	9 mm
Overhang $L_1$	60 mm
suitable indexable insert	SC.. 09T3..
Setting angle $\kappa$	75 degrees
ISO code toolholder	A20Q SSKCR/L09
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Pack of insert screws	269028 8
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500