

Garant
eco screw-on toolholder, right-hand, Shank size / insert size: 20/16mm

Order data

Order number	261304 20/16
GTIN	4045197945211
Item class	21U

Description
Version:

GARANT eco system screw-on toolholder with internal coolant feed to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability. With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No.317900 – 319886.

Through-coolant: yes

ISO code toolholder: SVJCR/L 2020X16

suitable indexable insert: VC.. 1604..

Functional width L₄: 25 mm

Head length L₁: 40 mm

Overall length L: 99 mm

Pack of insert screws: 269023 3

Technical description

Shank size	20 mm
ISO code toolholder	SVJCR/L 2020X16
Shim	259033 5
Overall length L	99 mm
Functional width L ₄	25 mm

Insert size	16 mm
Shim screw	269013 1
suitable indexable insert	VC.. 1604..
Head length L ₁	40 mm
Pack of insert screws	269023 3
Series	Eco
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15