

Garant
eco screw-on toolholder, right-hand, Shank size / insert size: 16/11mm

Order data

Order number	261304 16/11
GTIN	4045197945198
Item class	21U

Description
Version:

GARANT eco system screw-on toolholder with internal coolant feed to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability. With flank face cooling.

Note:

Coolant transfer only in conjunction with GARANT eco-system toolholders No.317900 – 319886.

Through-coolant: yes

ISO code toolholder: SVJCR/L 1616X11

suitable indexable insert: VC.. 1103..

Functional width L_4 : 20 mm

Head length L_1 : 34 mm

Overall length L: 81 mm

Pack of insert screws: 269023 1

Technical description

Pack of insert screws	269023 1
suitable indexable insert	VC.. 1103..
Insert size	11 mm
Overall length L	81 mm
Shank size	16 mm

Head length L ₁	34 mm
Functional width L ₄	20 mm
ISO code toolholder	SVJCR/L 1616X11
Series	Eco
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	93 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8