

**Garant**

**Side lock arbor Nickel-plated, with cooling channel bore, HSK-A 63 short,  
Clamping  $\varnothing$  D1: 10mm**


**Order data**

Order number	304272 10
GTIN	4045197945570
Item class	31A

**Description**
**Version:**

- **With RFID/Balluffchip bore.**
- **HSK mating faces machined.**

**GARANT:** All shanks hard turned (for smooth running!).  
Special nickel plating.

**With coolant supply holes that can be plugged.**

**Application:**

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

**Optional extras:**

Coolant pipe No. 309880, coolant pipe wrench No. 309890

**Note:**

HSK 40 and 50, Form A and E available ex works by the manufacturer.

**Technical description**

External $\varnothing$ D	35 mm
Spare clamping screw No. 30 9900	10
Overhang dimension A	65 mm
Clamping $\varnothing$ D <sub>1</sub>	10 mm
Adapter	HSK-A 63 short

Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-4
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping  $\varnothing$  D1 10 mm

309900 10