

Garant

**Side lock arbor Nickel-plated, with cooling channel bore, HSK-A 63 short,
Clamping \varnothing D1: 16mm**



Order data

Order number	304272 16
GTIN	4045197945594
Item class	31A

Description

Version:

- With RFID/Balluffchip bore.
- HSK mating faces machined.

GARANT: All shanks hard turned (for smooth running!).
Special nickel plating.

With coolant supply holes that can be plugged.

Application:

For clamping tools with Weldon shank to DIN 1835 Form B and DIN 6535 Form HB.

Optional extras:

Coolant pipe No. 309880, coolant pipe wrench No. 309890

Note:

HSK 40 and 50, Form A and E available ex works by the manufacturer.

Technical description

Overhang dimension A	80 mm
External \varnothing D	48 mm
Clamping \varnothing D ₁	16 mm
Spare clamping screw No. 30 9900	16
Adapter	HSK-A 63 short

Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-4
Arbor standard	DIN 69893
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping \varnothing D1 16 mm	309900 16
--	-----------