

Garant**Toolholder for metric profile broaching tools $\varnothing d = 8$ mm, Shank $\varnothing D_S$: 20mm**

Order data

Order number	293020 20
GTIN	4045197945907
Item class	29K

Description

Suitable for:

CNC and conventional machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MT2, MT3 and MT4.

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

L	38 mm
Shank length L_s	50 mm
Shank type	Plain shank
Shank $\varnothing D_S$	20 mm
$\varnothing D$	33 mm

Ø d	8 mm
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool