

Garant**Toolholder for metric profile broaching tools $\varnothing d = 8$ mm, Shank $\varnothing DS$: MK2mm**

Order data

| | |
|--------------|---------------|
| Order number | 293020 MK2 |
| GTIN | 4045197945921 |
| Item class | 29K |

Description

Suitable for:

CNC and conventional machines.

Optional extras:

Positioning aid (No. 293000) and pin wrench (No. 293006).

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MT2, MT3 and MT4.

Note:

- **Caution: Always use appropriate slotting tool \varnothing .**
- **Other shank connections on request.**

Technical description

| | |
|--------------------|-------|
| L | 38 mm |
| Shank length L_s | 69 mm |
| Shank type | MT2 |
| $\varnothing D$ | 33 mm |

| | |
|-----------------|--|
| Ø d | 8 mm |
| Arbor size | MT2 |
| Through-coolant | no |
| Type of product | Keyway broaching and profile slotting tool |

Accessories

| | |
|--------------------------------|-----------|
| Pin spanner for holder Ø 16 mm | 293006 16 |
| Pin spanner for holder Ø 5 mm | 293006 5 |
| Pin spanner for holder Ø 12 mm | 293006 12 |
| Pin spanner for holder Ø 8 mm | 293006 8 |