

**Garant**

**Toolholder for metric profile broaching tools  $\varnothing d = 16$  mm, Shank  $\varnothing DS$ : 25mm**


**Order data**

Order number	293026 25
GTIN	4045197945990
Item class	29K

**Description**
**Suitable for :**

CNC and conventional machines.

**Optional extras:**

Positioning aid (No. 293000) and pin wrench (No. 293005) available ex stock.

Drive-out tang for MT shanks can be ordered under No. 293008 in the sizes MK2, MK3 and MK4.

**Note:**

- **Caution: Always use appropriate slotting tool  $\varnothing$ .**
- **Other shank connections on request.**

L: 76 mm

Shank length  $L_s$ : 50 mm

$\varnothing D$ : 58 mm

**Technical description**

L	76 mm
Shank length $L_s$	50 mm

Shank type	Plain shank
Shank $\varnothing D_s$	25 mm
$\varnothing D$	58 mm
$\varnothing d$	16 mm
Through-coolant	no
Type of product	Keyway broaching and profile slotting tool