

Garant**Profile broaching insert, hex socket metric $\varnothing d = 16$ mm, TiN, Hexagon: 5mm****Order data**

Order number	293046 5
GTIN	4045197946621
Item class	29L

Description**Version:**

With TiN coating.

Application:For generation of profiles **in a single pass**.**Suitable for :**

Profile broaching holder No. 293020 – 293079.

Note:

- **Special sizes and special profiles available in request.**
- **Detailed application values can be found in the info block on page 806.**

Note re advertising text:

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in the info block on page 727 in the catalogue Vol. 1.**

L₁: 40 mm

L: 8.5 mm

Tolerance: + 0.12 to + 0.15 mm

Technical description

L	8.5 mm
Width across flats	5 mm
Tool material	HSS
Tolerance	+ 0.12 to + 0.15 mm
Profile	Hexagon
L ₁	40 mm
Ø d	16 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool