

Garant

Profile broaching insert internal Torx® Ø d = 16 mm, TiN, Torx® profile: TX40mm



Order data

Order number	293066 TX40
GTIN	4045197947628
Item class	29L

Description**Version:**

With TiN coating.

Application:

For generation of profiles **in a single pass.**

Suitable for :

Profile broaching holder No. 293020 – 293079.

Note:

- **Special sizes and special profiles available in request.**
- **Detailed application values can be found in the info block on page 806.**

Note re advertising text:

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in the info block on page 727 in the catalogue Vol. 1.**

L₁: 40 mm

L: 5 mm

Tolerance: - 0.01 to + 0.01 mm

Technical description

L	5 mm
Pre-drill Ø	5 mm
Torx® tumbling external diameter	6.78 mm
Tool material	HSS
Torx® profile	TX40
Tolerance	- 0.01 to + 0.01 mm
Profile	Torx®
L ₁	40 mm
Ø d	16 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool