

**Garant****Profile broaching insert internal Torx® Ø d = 8 mm, TiN, Torx® profile: TX15mm****Order data**

Order number	293060 TX15
GTIN	4045197947369
Item class	29L

**Description****Version:**

With TiN coating.

**Application:**

For generation of profiles **in a single pass.**

**Suitable for:**

Profile broaching holder No. 293020 – 293079.

**Note:**

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in our application ToolScout.**

**Technical description**

L	3 mm
Torx® tumbling external diameter	3.37 mm
Pre-drill Ø	2.5 mm
Tool material	HSS

Torx® profile	TX15
Tolerance	- 0.005 to + 0.01 mm
Profile	Torx®
L <sub>1</sub>	18 mm
Ø d	8 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool