

Garant

Profile broaching insert internal Torx® Ø d = 12 mm, TiN, Torx® profile: TX25mm



Order data

Order number	293063 TX25
GTIN	4045197947482
Item class	29L

Description

Version:

With TiN coating.

Application:

For generation of profiles **in a single pass.**

Suitable for:

Profile broaching holder No. 293020 – 293079.

Note:

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in our application ToolScout.**

Technical description

L	4 mm
Torx® tumbling external diameter	4.54 mm
Pre-drill Ø	3.35 mm
Tool material	HSS

Data sheet

Torx® profile	TX25
Tolerance	- 0.005 to + 0.01 mm
Profile	Torx®
L ₁	25 mm
Ø d	12 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool