

**Garant**

**Profile broaching insert internal Torx® Ø d = 16 mm, TiN, Torx® profile: TX25mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 293066 TX25   |
| GTIN         | 4045197947598 |
| Item class   | 29L           |

**Description****Version:**

With TiN coating.

**Application:**

For generation of profiles **in a single pass.**

**Suitable for:**

Profile broaching holder No. 293020 – 293079.

**Note:**

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in our application ToolScout.**

**Technical description**

|                                  |         |
|----------------------------------|---------|
| L                                | 4 mm    |
| Pre-drill Ø                      | 3.35 mm |
| Torx® tumbling external diameter | 4.54 mm |
| Tool material                    | HSS     |

|                 |  |
|-----------------|--|
| Torx® profile   | TX25                                       |
| Tolerance       | - 0.005 to + 0.01 mm                       |
| Profile         | Torx®                                      |
| L <sub>1</sub>  | 40 mm                                      |
| Ø d             | 16 mm                                      |
| Coating         | TiN  |
| Type of product | Keyway broaching and profile slotting tool |