

Garant**Profile broaching insert internal Torx® Ø d = 8 mm, TiN, Torx® profile: TX10mm****Order data**

Order number	293060 TX10
GTIN	4045197947352
Item class	29L

Description**Version:**

With TiN coating.

Application:

For generation of profiles **in a single pass.**

Suitable for:

Profile broaching holder No. 293020 – 293079.

Note:

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in our application ToolScout.**

Technical description

L	2 mm
Torx® tumbling external diameter	2.83 mm
Pre-drill Ø	2.1 mm
Tool material	HSS

Torx® profile	TX10
Tolerance	- 0.005 to + 0.01 mm
Profile	Torx®
L ₁	18 mm
Ø d	8 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool