

**Garant****Profile broaching insert internal Torx® Ø d = 8 mm, TiN, Torx® profile: TX7mm****Order data**

Order number	293060 TX7
GTIN	4045197947338
Item class	29L

**Description****Version:**

With TiN coating.

**Application:**For generation of profiles **in a single pass**.**Suitable for:**

Profile broaching holder No. 293020 – 293079.

**Note:**

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in our application ToolScout.**

**Technical description**

L	1.7 mm
Torx® tumbling external diameter	2.08 mm
Pre-drill Ø	1.5 mm
Tool material	HSS

Torx® profile	TX7
Tolerance	0.0 to +0.01 mm
Profile	Torx®
L <sub>1</sub>	18 mm
Ø d	8 mm
Coating	TiN
Type of product	Keyway broaching and profile slotting tool