

Garant

Profile broaching insert internal Torx® Ø d = 16 mm, TiN, Torx® profile: TX50mm

**Order data**

| | |
|--------------|---------------|
| Order number | 293066 TX50 |
| GTIN | 4045197947659 |
| Item class | 29L |

Description**Version:**

With TiN coating.

Application:

For generation of profiles **in a single pass.**

Suitable for:

Profile broaching holder No. 293020 – 293079.

Note:

- **Special sizes and special profiles available on request.**
- **Detailed application values can be found in our application ToolScout.**

Technical description

| | |
|----------------------------------|---------|
| L | 6 mm |
| Torx® tumbling external diameter | 8.97 mm |
| Pre-drill Ø | 6.6 mm |
| Tool material | HSS |

| | |
|-----------------|--|
| Torx® profile | TX50 |
| Tolerance | - 0.01 to + 0.01 mm |
| Profile | Torx® |
| L ₁ | 40 mm |
| Ø d | 16 mm |
| Coating | TiN |
| Type of product | Keyway broaching and profile slotting tool |