

 **HALDER****Centring clamping element with clamping segments, Type: 5****Order data**

Order number	370017 5
GTIN	4030618238768
Item class	37K

**Description****Advantage:**

- **Precise self-centring with an accuracy of  $\pm 0.025$  mm.**
- **The clamping elements allow components with rough or machined surfaces to be positively centred and pulled down at the seating point.**
- **Large adjustment range even at low overall height.**
- **Can be bolted on from above or below.**

**Application:**

For centring and clamping components with a location bore.

**Material:**

Base of tool steel, hardened, burnished. Clamping elements of stainless steel 1.4112, hardened and ground.

**Technical description**

$D_{\min}$	30.5 mm
$D_{\max}$	38.5 mm
$\varnothing d_4$	M6 mm
$h_4$	7 mm

Clamping force	5 kN
$h_2$	15.2 mm
$d_3 f7$	25 mm
$h_5$	33.4 mm
Type of product	Jig clamping system