

HALDER**Centring clamping element with clamping segments, Type: 3****Order data**

Order number	370017 3
GTIN	4030618238744
Item class	37K

Description**Advantage:**

- **Precise self-centring with an accuracy of ± 0.025 mm.**
- **The clamping elements allow components with rough or machined surfaces to be positively centred and pulled down at the seating point.**
- **Large adjustment range even at low overall height.**
- **Can be bolted on from above or below.**

Application:

For centring and clamping components with a location bore.

Material:

Base of tool steel, hardened, burnished. Clamping elements of stainless steel 1.4112, hardened and ground.

Technical description

$\varnothing d_4$	M6 mm
D_{max}	26.5 mm
Clamping force	5 kN
h_4	6 mm

h_2	15.1 mm
D_{\min}	22.5 mm
$d_3 f7$	20 mm
h_5	29.1 mm
Type of product	Jig clamping system