

HALDER**Single taper clamping jaw flat, Thread M: M8****Order data**

Order number	370022 M8
GTIN	4030618237686
Item class	37K

Description**Application:**

Turning the clamping screw moves the two clamping jaws outwards and presses the workpieces against a fixed stop.

Material:

Base of tool steel, hardened, bright finish. Base of tool steel, hardened, burnished and ground.

Note:

Installation in a tapped hole or using a nut on T-slots. Horizontal or vertical multiple clamping can be performed.

Technical description

Length	27 - 31 mm
Clamping force	20 kN
maximum tightening torque	43 Nm
Thread M	M8
B ₁	29 mm
Height H	17.5 mm

Type of product

Wedge clamp