

**HALDER****Single taper clamping jaw flat, Thread M: M12****Order data**

Order number	370022 M12
GTIN	4030618237693
Item class	37K

**Description****Application:**

Turning the clamping screw moves the two clamping jaws outwards and presses the workpieces against a fixed stop.

**Material:**

Base of tool steel, hardened, bright finish. Base of tool steel, hardened, burnished and ground.

**Note:**

Installation in a tapped hole or using a nut on T-slots. Horizontal or vertical multiple clamping can be performed.

**Technical description**

Clamping force	30 kN
Thread M	M12
maximum tightening torque	85 Nm
B <sub>1</sub>	41 mm
Length	42 - 49 mm
Height H	26 mm

Type of product

Wedge clamp