

HALDER**Single taper clamping jaw ribbed, Thread M: M12****Order data**

Order number	370021 M12
GTIN	4030618237662
Item class	37K

Description**Application:**

Turning the clamping screw moves the two clamping jaws outwards and presses the workpieces against a fixed stop.

Material:

Base of tool steel, hardened, bright finish. Base of tool steel, hardened, burnished and ground.

Note:

Installation in a tapped hole or using a nut on T-slots. Horizontal or vertical multiple clamping can be performed.

Technical description

Length	42 - 49 mm
B ₁	41 mm
maximum tightening torque	85 Nm
Thread M	M12
Clamping force	30 kN
Height H	26 mm

Type of product

Wedge clamp