



Pitbull clamp blunt edge, Thread M: M2,5



Order data

Order number	370030 M2,5
GTIN	4046368563104
Item class	37M

Description

Version:

- **Clamp with socket-head screw to DIN912, with oil-tight O-ring.**
- **Secure and precise clamping.**
- **Compact size, so few interference contours.**

Blunt edge for general tasks.

Application:

Ideal for multiple clamping.

Technical description

Clamping width	9.5 mm
Material	Steel
H	6.6 mm
Clamping force	2.8 kN
B _{H9}	9.5 mm
H ₁	3.6 mm

Clamping travel	0.15 mm
B ₁	3.8 mm
maximum tightening torque	1.8 Nm
Thread M	M2.5
Height H ₂	1.9 mm
Type of product	Jig clamping system